

# ACCURATE FILMS for Accessories

ACCURATE FILMS		HRD			AFP	ARS	AGB	BLC
Base Film(μm)		50	100		100	100	100	100
Adhesive Strength	Adsorption level	High	Mid	High	Mid	Mid	High	Mid
Surface Finish	High Transparency	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>		<input type="radio"/>
	Low Inteference	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>		
	Hard coat (Antiscratch)	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>
	Reinstallable	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>
	Antifingerprint				<input checked="" type="radio"/>		<input type="radio"/>	<input type="radio"/>
	Antiglare (glossy)					<input type="radio"/>		
	Antiglare (matte)						<input type="radio"/>	
	Antimicrobial						<input type="radio"/>	
	Blue Light Reduction							<input type="radio"/>
	Absorb tiny bubbles							<input type="radio"/>
Custom Sizes		Yes	Yes	Yes	Yes	Yes	Yes	Yes

